



M - motor
TR - transformer
PH - photocell
SV - solenoid valve

~~Munters Italy S.p.A.~~
 APPROVED
 TECHNICAL DEPT.
 08 FEB 2012

| Rev.No | Date | Description | Drawer |
|--------|------------|--------------------------------|-------------|
| 01 | 08/02/2012 | Reviewed the wires connections | B. Fulcheri |
| 00 | 25/10/2011 | First issue | D. Fulcheri |

| Linear dimension range | up to 6 | over 6 up to 30 | over 30 up to 120 | over 120 up to 400 | over 400 up to 1000 | over 1000 up to 2000 | over 2000 up to 4000 |
|------------------------|---------|-----------------|-------------------|--------------------|---------------------|----------------------|----------------------|
| tolerance limits | ±0.3 | ±0.5 | ±0.8 | ±1.2 | ±2 | ±3 | ±4 |

| | | | | | |
|--|--|---|--|---|--|
| Description | | Schema elettrico XCM XCM wiring diagram | | Drawing No 09D01S | |
| Material | | - | | File name 09D01S01 | |
| | | Designer F. Trifoglio | | Purchased part No - | |
| | | Drawer D. Fulcheri | | Manufactured part No - | |
| | | Latest revision approved by F. Trifoglio | | | |
| | | Date 25/10/2011 | | | |
| MUNTERS ITALY S.p.A. - Mondovi <small>This drawing is exclusive property of MUNTERS ITALY S.p.A. Any vision, reproduction or release without written authorization by MUNTERS ITALY S.p.A. is ABSOLUTELY FORBIDDEN</small> | | Thickness - mm Weight - kg | | DIMENSIONS WITHOUT TOLERANCE LIMITS: ROUGH PRECISION LEVEL UNI EN 22768-1/2 | |
| | | | | Drawing scale 1:1 Paper size A4 | |