



400V 22kW

T - Thermostat
 B - Switch
 M - Motor
 TV - Safety thermostat
 D - Heating element
 T1 - Time-delay thermostat
 J1 / J2 - Relay

SWITCH

- ⊖ OFF
- ⊗ POS.5
- ⊕ POS.5+2
- ⊕⊗ POS.5+2+3

0					0°
1	⊗				90°
2	⊗	⊗			180°
3	⊗	⊗	⊗		270°

00	04/12/09	First issue					D. Fulcheri
Rev.No	Date	Description					Drawer
Linear dimension range	up to 6	over 6 up to 30	over 30 up to 120	over 120 up to 400	over 400 up to 1000	over 1000 up to 2000	over 2000 up to 4000
tolerance limits	±0.3	±0.5	±0.8	±1.2	±2	±3	±4

Description
Schema elettrico RPL 22 FT (made in China)
RPL 22 FT wiring diagram (made in China)

Material: - Thickness: -mm Drawer: **D. Fulcheri**

Weight: -kg Latest revision approved by: *[Signature]*

Drawing scale: - Date: **04/12/2009**

Munters
 MUNTERS ITALY S.p.A. - Mondovi

This drawing is exclusive property of MUNTERS ITALY S.p.A.. Any vision, reproduction or release without written authorization by MUNTERS ITALY S.p.A. is ABSOLUTELY FORBIDDEN

DIMENSIONS WITHOUT TOLERANCE LIMITS:
 ROUGH PRECISION LEVEL
 UNI EN 22768-1/2

Drawing No	SCH092
File name	SCH09200
Purchased part No	-
Manufactured part No	-