

## Product sheet Smart Controllers

### Features

- Automatic control of ventilation, cooling, and heating
- Supports
  - Temperature and humidity sensors
  - Water and feed meters
  - Potentiometer feedback
  - Wind speed and direction sensor for natural ventilation
  - Digital inputs
  - Analog 0-10 VDC outputs
  - TRIAC for variable speed fans
  - History data on PC
  - Data plug for easy transfer of settings
  - Multiple language packages

### Benefits

- Cost effective technology provides high ROI.
- Automatic shift from minimum ventilation to tunnel ventilation ensures high air quality at any temperature.
- User friendly software and flexible settings enable adjusting the SMART to specific local conditions.
- Supported by Munters PC communication software, enabling remote access and ability to supervise 24/7.
- SMART models vary in their number of relays and options, enabling you to find the model that meets your specific requirements.

# Smart Controllers

## Cost Effective Climate Controllers

Munters SMART Controllers provide the poultry and pig industries with a cost-effective climate control solution that is easy to install, simple to program, and built to work in the rigorous conditions found in poultry and swine houses.











Smart

## INPUT

-  Up to three Temperature Sensors
-  Humidity Sensor
-  Feed Counters
-  Wind Speed
-  Potentiometers
-  Water Meter



## OUTPUT

-  Light
-  Two Curtains
-  Three Timers
-  Cooling System
-  Alarm
-  Floor and Room Heaters
-  Up to seven Fan Groups
-  Variable Speed Fan

## LOCAL NETWORKS

-  Wired
-  Wireless

**Australia** Phone +61 2 8843 1594, [agh.info@munters.com.au](mailto:agh.info@munters.com.au), **Brazil** Phone +55 41 3317 5050, [contato@munters.com](mailto:contato@munters.com), **Canada** Phone +1 517 676 7070, [aghort.info@munters.com](mailto:aghort.info@munters.com), **China** Phone +86 10 8048 3493, [marketing@munters.cn](mailto:marketing@munters.cn), **Denmark** Phone +45 98 623 311, [aghort@munters.dk](mailto:aghort@munters.dk), **Germany** +49 (0) 25 58 - 93 92-0, **India** Phone +91 20 6681 8900, [info@munters.in](mailto:info@munters.in), **Indonesia** Phone +66 2 642 2670, [info@munters.co.th](mailto:info@munters.co.th), **Israel** Phone +972 3 920 6200, [info@munters.co.il](mailto:info@munters.co.il), **Italy** Phone +39 0183 5211, [info@munters.it](mailto:info@munters.it), **Japan** Phone +81 3 5970 0021, [mkk@munters.jp](mailto:mkk@munters.jp), **Korea** Phone +82 2 7618 701, [munters@munters.co.kr](mailto:munters@munters.co.kr), **Mexico** Phone +52 818 2625 400, [dhinfo@munters.com](mailto:dhinfo@munters.com), **Singapore** Phone +65 7 446 828, [info@munters.com.sg](mailto:info@munters.com.sg), **South Africa and Sub-Sahara Countries** Phone +27 11 997 2000, [info@munters.co.za](mailto:info@munters.co.za), **Spain** Phone +39 0183 5211, [info@munters.it](mailto:info@munters.it), **Sweden** Phone +46 8 6266 300, [info@munters.se](mailto:info@munters.se), **Thailand** Phone +66 2 6422 670, [info@munters.co.th](mailto:info@munters.co.th), **Turkey** Phone +90 262 7513 750, [info@muntersform.com](mailto:info@muntersform.com), **USA** Phone +1 517 676 7070, [aghort.info@munters.com](mailto:aghort.info@munters.com), **Export & Other countries** Phone +39 0183 5211, [info@munters.it](mailto:info@munters.it)



Your closest distributor