



Item	Catalog No.	Description	Qty.
1	FH1951	Orifice Panel, GZ	1
2	FH2919	Top Housing Panel with Shutter Clips, GZ	1
3	FH2920	Left Side Housing Panel with Shutter Clips, GZ	1
4	FH2918	Bottom Housing Panel with Shutter Clips, GZ	1
5	FH2921	Right Side Housing Panel with Shutter Clips, GZ	1
6	FP2548	Prop Assembly, 3-Blade, 25mm, SS	1
	FP2549	Prop Assembly, 3-Blade, GZ	1
7	FH2429	Support Bracket for Motor Mounting Plate, GZ	1
8	FH2427	Mounting Plate for NEMA 56 Frame Motor, GZ	1
9	FH2428	Center Support Brace for Strut, GZ	1
10	FM1024*	Motor, 1HP, 1725 RPM, 56Fr, 1ph., 120/240V	1
11	FH1302	Reinforcement Brackets for Strut, GZ	2
12	KN1860	Hex Nut, M25x10mm, ZP	1
13	KX1208	Cover Cap, Black, PL	1
14	FH1930	Center Strut, GZ	1
15	FH1932	Spacer Plate, PL	2
16	FH1505*	V-Belt, 87" A-Section	1
17	KX1130	Shaft Shield for Prop Sheave, AL	1
18	FH2137*	Propeller Sheave, AL	1
19	FP2060	Hub with Bearing and Shaft	1
20	FH2505	Mounting Bracket for Belt Tensioner, CTD-GZ	1
21	FH2402K	Belt Tensioner Assembly with 3" Idler Pulley	1
	FH2406	3" Idler Pulley only, with Bolt	1
	FH2439	Tensioner Arm only, AL	1
22	FH2138*	Motor Sheave, AK35x $\frac{5}{8}$ " Bore with Keyseat, CI	1
23	FH2130	Cone Support Brackets, GC Type, GZ	4
24	FH4250	Discharge Cone (1 section), GZ	4
25	KX1256	Spacer 0.32"ID x 0.75"OD x 1"L., Black, NY	12
26	FH2648	Guard, PVC Coated	1
27	PZ48 or GS48 or SW54	Shutter, 53 $\frac{7}{8}$ " Sq., PL or GZ or AL	1

* Parts listed are for standard configuration with 1 HP motor and other drive components operating on 60Hz power. Contact office for replacement part numbers for your fan configuration.