



Product Sheet Rlink One

Features

- Operates at frequencies and power levels that do not require a license
- Rlink One can function in multiple roles:
 - Signal transmission to and from controllers
 - Repeater unit enhancing signal strength
 - Testing the network signal during setup or troubleshooting
- Multiple:
 - Transmission rates (from 1200 to 115K BPS)
 - Channel addresses (up to 10)
 - Power levels (from 10 mW to 1W)
- Setup configuration maintained in the event of a power failure
- Automatic reconfiguration in case of total signal loss
- Self-tests for low signal levels
- Surge and EMC protection
- Backward compatible
- Supports multiple network topologies

Benefits

- Supports loopback signal transmission, enabling you to test antennas and locations before installing controllers or other communication units
- Adjustable power levels minimize signal interference from adjoining networks
- Improved user interface and multiple LEDs simplify troubleshooting in every aspect of signal transmission
 - RF strength indicators
 - Receiver – Transmitter communication
 - Internal communication
 - Improved electronics ensures signal stability

Rlink One

Long Distance RF, Simple Installation and Usage

Munter's Rlink One Communication unit provides wireless communication between a controller network and a communication system. The Rlink One provides an effective alternative for situations when connecting the controllers to the communication network via a communication cable is not feasible. Rlink One's multiple new features ensure RF signal quality, enable long distance transmission, and greatly simplify installation and setup.



Rlink One





[Australia](#) Phone +61 2 8843 1594, aghort@munters.com.au, [Brazil](#) Phone +55 41 3317 5050, contato@munters.com,
[Canada](#) Phone +1 517 676 7070, aghort@munters.com, [China](#) Phone +86 10 8048 3493, marketing@munters.cn,
[Denmark](#) Phone +45 98 623 311, aghort@munters.dk, [Germany](#) +49 (0) 25 58 - 93 92-0, [India](#) Phone +91 20 6681 8900, info@munters.in, [Indonesia](#) Phone +66 2 642 2670, info@munters.co.th, [Israel](#) Phone +972 3 920 6200, info@munters.co.il, [Italy](#) Phone +39 0183 5211, info@munters.it, [Japan](#) Phone +81 3 5970 0021, mkk@munters.jp,
[Korea](#) Phone +8227618701, munters@munters.co.kr, [Mexico](#) Phone +528182625400, dhinfo@munters.com,
[Singapore](#) Phone +65 7 446 828, info@munters.com.sg, [South Africa and Sub-Sahara Countries](#) Phone +27 11 997 2000, info@munters.co.za,
[Spain](#) Phone +39 0183 5211, info@munters.it, [Sweden](#) Phone +46 8 6266 300, info@munters.se,
[Thailand](#) Phone +66 2 6422 670, info@munters.co.th, [Turkey](#) Phone +90 262 7513 750, info@muntersform.com, [USA](#) Phone +1 517 676 7070, aghort@munters.com, [Export & Other countries](#) Phone +39 0183 5211, info@munters.it



Your closest distributor