

#### Product sheet

#### ML Series with Climatix ML1350 Desiccant dehumidifier

- Modern Climatix control system
- Small footprint requires minimal floor area
- High airflow capacity
- Minimal energy consumption
- Unique plastic rotor casing
- 100% corrosion resistance
- Dehumidifies efficient down to -20 °C
- Communication and external control options

## ML1350 with Climatix

The ML1350 desiccant dehumidifier with climatix control is designed to efficiently dehumidify in low moisture applications.

It is equipped with an internally sealed rotor unit. The rotor casing is constructed of durable thermoset plastic and contains isolated sections that provide a precise balance for dehumidification, reactivation, and heat recovery airflows. Its rugged formed metal frame and access panels are produced from corrosion resistant Aluzink®.


The modern control system conforms to EN 60204 (IEC204) standards and is equipped with a number of alarm functions to ensure total control of the dehumidification process.

ML Series dehumidifiers conform to both harmonised European Standards and to CE marking specifications.



ML with Climatix Controls

## Dimensions




Width A	Depth B	Height C	Diam. D	Diam. E	Weight
720mm	600mm	1510mm	250mm	160mm	169kg

Measurement diagram for reference only.

## Technical specifications

Process Air	
Rated airflow (m <sup>3</sup> /h)	1350
Available static pressure (pa)	300
Reactivation air	
Rated airflow (m <sup>3</sup> /h)	490
Available static pressure (pa)	300
Total Power Voltage & Current (amps & phase)	
Total power (kW) Electrical	15.16
380V 3-50Hz (A)	24.4
380V 3-60Hz (A)	24.9
400V 3-50Hz (A)	23.6
415V 3-50Hz (A)	23.1
440V 3-60Hz (A)	22.3
460V 3-60Hz (A)	21.7
480V 3-60Hz (A)	21.1
Miscellaneous Data	
Operating temperature (°C)	-20/+40
Sound power level to room Lw(A) dB, all inlets and outlets ducted	75
Air filter standard	G4
IEC protective class (unit)	IP33
IEC protective class (electrical)	IP54

## Dehumidification Capacity



## Options

- Communication via Modbus, BACnet
- Dewpoint sensor
- External controls
- External Filter Box M5 or F7
- Insulated process air inlet
- Mirror handed
- Stainless steel casing

For more information visit [munters.com](http://munters.com)



**Australia** Phone +61 2 8843 1588, [dh.info@munters.com.au](mailto:dh.info@munters.com.au) **Austria** Phone +43 1 6164298-92-51, [lufentfeuchtung@munters.at](mailto:lufentfeuchtung@munters.at) **Belgium** Phone +32 1528 5611, [info@muntersbelgium.be](mailto:info@muntersbelgium.be) **Brazil** Phone +55 41 3317 5050, [munters@com.br](mailto:munters@com.br) **Canada** Phone +1 905 564 6466, [dhinfo@munters.com](mailto:dhinfo@munters.com) **China** Phone +86 10 8048 3493, [info@munters.com.cn](mailto:info@munters.com.cn) **Czech Republic** Phone +420 775 569 657, [info@munters-odvlhcovani.cz](mailto:info@munters-odvlhcovani.cz) **Denmark** Phone +45 4495 3355, [info@munters.dk](mailto:info@munters.dk) **Finland** Phone +358 20 776 8230, [laitemyyni@munters.fi](mailto:laitemyyni@munters.fi) **France** Phone +33 1 3411 5757, [dh@munters.fr](mailto:dh@munters.fr) **Germany** Phone +49 4087 96900, [mgd@munters.de](mailto:mgd@munters.de) **India** Phone +91 20 668 18 900, [info@munters.in](mailto:info@munters.in) **Italy** Phone +39 0183 52 11, [marketing@munters.it](mailto:marketing@munters.it) **Japan** Phone +81 3 5970 0021, [mkk@munters.co.jp](mailto:mkk@munters.co.jp) **Korea** +82 2761 8701, [munters@munters.co.kr](mailto:munters@munters.co.kr) **Mexico** Phone +52 81 8262 5400, [munters@munters.com.mx](mailto:munters@munters.com.mx) **Netherlands** Phone +31 172 433231, [vochtbeheersing@munters.nl](mailto:vochtbeheersing@munters.nl) **Poland** Phone +48 58305 3517, [dh@munters.pl](mailto:dh@munters.pl) **Singapore** Phone +65 6744 6828, [info@munters.com.sg](mailto:info@munters.com.sg) **South Africa** Phone +27 11 971 9700, [info@munters.co.za](mailto:info@munters.co.za) **Spain** Phone +34 91 640 09 02, [marketing@munters.es](mailto:marketing@munters.es) **Sweden** Phone +46 8 626 63 00, [avfukning@munters.se](mailto:avfukning@munters.se) **Switzerland** Phone +41 52 343 8886, [info.dh@munters.ch](mailto:info.dh@munters.ch) **Thailand** Phone +66 2642 2670, [info@munters.co.th](mailto:info@munters.co.th) **Turkey** Phone +90 262 751 3750, [info@muntersform.com](mailto:info@muntersform.com) **UAE** +971 4 8809295, [middle.east@munters.com](mailto:middle.east@munters.com) **United Kingdom** Phone +44 1480 432 243, [dryair@munters.co.uk](mailto:dryair@munters.co.uk) **USA** Phone +1 978 241 1100, [dhinfo@munters.com](mailto:dhinfo@munters.com) **Vietnam** Phone +84 8 8256 838, [vietnam@muntersasia.com](mailto:vietnam@muntersasia.com)

