



Product description
MRC: Munters Roller Curtain

- Curtain protects against wind and severe weather conditions
- Variable opening
- Manufactured in UV resistant PVC coated high tenacity polyester
- Anti-static treatment repels dirt (straw, sand, dust)
- Optimal light transmission
- Operated either manually, semi-automatic or fully automatic
- Curtain opens from top down

MRC: Munters Roller Curtain

Munters MRC is developed for use in Dairy, Swine and Poultry installations. The curtain combines ventilation requirements with ease of operation and value for money. The curtain can replace an entire outer wall (or parts of) on the building.

A principal feature of the curtain is that it is coiled on the bottom profile so that it can be rolled down completely, thus providing a full view of the surroundings, or alternatively it can be closed completely or rolled down to any point between fully closed and fully open.

Munters A/S,
Nordvestvej, 3 - 9600 Aars, Denmark / Phone +45 986 233 11 / Fax +45 986 213 54 /
www.munters.dk/agro



Product description

Munters MRC is manufactured in heavy duty, UV resistant PVC coated high tenacity polyester. The light grey color ensures optimal light transmission. The curtain is anti-static and will repel dirt (sand, straw, dust).

The curtain rolls on an extruded aluminum profile.

As safety against strong winds, specially designed wind pipes are installed at intervals of 2 meters (recommended distance – distance varies depending on opening height). The wind pipes are made of galvanized iron with an outer plastic pipe – the latter to minimize wear and tear on both wind pipe and curtain. Wind pipes are installed on the outside and inside of the curtain, acting as a guide for the curtain.

To minimize draft from the sides of the curtain, specially designed wind screens are installed on both sides of each curtain section.

The curtain is equipped with a strap pulling system, which can be operated vertically by gear motor. It is possible to choose between semi-automatic operation, where you decide when the curtain moves up or down, or a fully automated operation, where the curtain is regulated by the Munters NaturalCenter/Master climate controller combined with a weather station.

Technical data

Max height	4 meter
Max length	100 m (max 300 m ² per section)
Power	3 phaset 400V
Function	Roll from top down
Accessories	Automatic regulation



Australien Munters Pty Limited, Phone. +61 2 8843 1594, **Brasilien** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation Mason, Phone +1 517 676 7070, **kina** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 3052 2520, **Indonesien** Munters, Phone +62 818 739 235, **Italien** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **Sydafrika & landene syd for Sahara** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spanien** Munters Spain S.A., Phone +34 91 640 09 02, **Sverige** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Tyrkiet** Munters Form Endüstri Sistemleri A.Ş., Phone +90 262 751 3750, **USA** Munters Corporation Mason, Phone +1 517 676 7070, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & other countries** Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication

© Munters, 2015

Your closest distributor