



Item	Catalog No.	Description	Qty.
1	FH1951	Orifice Panel, GZ	1
2	FH4061	Top Housing Panel, GZ	1
3	FH4062	Left/Right Side Housing Panel, GZ	1
4	FH4060	Bottom Housing Panel, GZ	1
5	FH4062	Left/Right Side Housing Panel, GZ	1
6	FP2549	Prop Assembly, 3-Blade, GZ	1
7	FH2429	Support Bracket for Motor Mounting Plate, GZ	1
8	FH2846	Mounting Plate for NEMA 56 Frame Motor, GZ	1
9	FH2428	Center Support Brace for Strut, GZ	1
10	FM1024*	Motor, 1HP, 1725 RPM, 56Fr, 1ph., 120/240V	1
11	FH1302	Reinforcement Brackets for Strut, GZ	2
12	KN1860	Hex Nut, M25x10mm, ZP	1
13	KX1208	Cover Cap, Black, PL	1
14	FH1930	Center Strut, GZ	1
15	FH1932	Spacer Plate, PL	2
16	FH1505*	V-Belt, 87" A-Section	1
17	KX1130	Shaft Shield for Prop Sheave, AL	1
18	FH2137	Propeller Sheave, AL	1
19	FP2060	Hub with Bearing and Shaft	1
20	FH2505	Mounting Bracket for Belt Tensioner, CTD-GZ	1
21	FH2402K	Belt Tensioner Assembly with 3" Idler Pulley	1
	FH2406	3" Idler Pulley only, with Bolt	1
	FH2439	Tensioner Arm only, AL	1
22	FH2138*	Motor Sheave, AK35x ⁵ / ₈ " Bore with Keyseat, CI	1
23	FH2130	Cone Support Brackets, GC Type, GZ	4
24	FH4349	Discharge Cone (Top/Bottom Section), GZ	2
	FH4450	Discharge Cone (Left/Right Section), GZ	2
25	FH2654	Guard, Flat Side Cone, 1/2 Circle, PVC Coated	2
26	FH1750	Inlet Guard, 56" Sq., 2" x 2", GZ	1
27	DG1050	Assembly, 4-Door Damper, 50" Fan	1
28	KX1459	Spring, Constant Force, 1"W., 1.15LB	2
29	AC2072	Spring Reel Spool, 2.75" O.D., 1.25"W., PL	2
30	FA2712	Tube Hinge, 26.2"L., AL	4
31	FA2722	50" Damper Door, Flat, GZ	2
	FA2724	50" Damper Door, Offset, GZ	2
32	FA1732	Short Wing Support Bracket, GZ	2
33	KX1043	⁵ / ₁₆ " Push-in Fastener, NY	4
34	FA1733	4-Door Damper Wing, PL	2
35	FA1730	Tall Wing Support Bracket, GZ	2
36	FH1965	Universal Shutter Clip, GZ	2
37	KX1015	Draw Latches, SS	2
38	FH1278	Guard Support Clips, GZ	2
39	KX1470	Retainer Spring, SS	2

* Parts listed are for standard configuration with 1HP motor and other drive components operating on 60Hz power. Contact office for replacement part numbers for your fan configuration.