

GREEN EC pH

EC pH Transmitter

FEATURES

- pH range: 0 – 14
- pH output: 4 – 20 mA
- EC range: 0 – 10 mS
- EC output: 4 – 20 mA
- EC sensor: pt100



Green EC pH Transmitter

Munters Green EC pH Transmitter transmits EC and pH sensor data to controllers, providing growers with data required for effective irrigation programs. The EC pH Transmitter converts the relevant signals into a 4 – 20 mA output, which is then sent to a Munters or third party controller.

The Transmitter can be ordered in two different containers:

- Plastic box: Wall mount unit, single EC pH readings
- Metal box: Panel mount unit, single or dual EC pH readings

Benefits:

- Controller's proven accuracy provides:
 - » Accurate, continual EC data helps increase yields
 - » pH measurement, preventing issues such as nutrient deficiencies or toxicity



GREEN EC pH

Configurator PN Munters Description

960-99-00043 EC electrode PT100 12 MM



Configurator PN Munters Description

960-99-00044 PH electrode Glass 12 MM
BNC connector



For more information on this
product go to:

munters.com

or

CONTACT YOUR BUSINESS UNIT



 **Munters**

Your closest distributor

Australia Phone +61 2 8843 1594, agh.info@munters.com.au, **Brazil** Phone +55 41 3317 5050, contato@munters.com,
Canada Phone +1 517 676 7070, aghort.info@munters.com, **China** Phone +86 10 8048 3493, marketing@munters.cn,
Denmark Phone +45 98 623 311, aghort@munters.dk, **Germany** +49 (0) 25 58 - 93 92-0, **India** Phone +91 20 6681 8900, info@munters.in, **Indonesia** Phone +66 2 642 2670, info@munters.co.th, **Israel** Phone +972 3 920 6200, info@munters.co.il, **Italy** Phone +39 0183 5211, info@munters.it, **Japan** Phone +81 3 5970 0021, mkk@munters.jp, **Korea** Phone +82 2 7618 701, munters@munters.co.kr, **Mexico** Phone +52 818 2625 400, dhinfo@munters.com,
Singapore Phone +65 7 446 828, info@munters.com.sg, **South Africa and Sub-Sahara Countries** Phone +27 11 997 2000, info@munters.co.za, **Spain** Phone +39 0183 5211, info@munters.it, **Sweden** Phone +46 8 6266 300, info@munters.se,
Thailand Phone +66 2 6422 670, info@munters.co.th, **Turkey** Phone +90 262 7513 750, info@muntersform.com, **USA** Phone +1 517 676 7070, aghort.info@munters.com, **Export & Other countries** Phone +39 0183 5211, info@munters.it

Munters reserves the right to make alterations to specifications, quantities, etc., for production or other reasons, subsequent to publication.

© Munters AB, 2019 - 190911