



Product sheet
Shutters and Insulated Closure Panels

Shutters

- PVC shutters are extremely affordable, durable, lightweight and open easily for minimal airflow resistance.
- Aluminum shutters offer a visually attractive appearance and are corrosion resistant.
- Heavy duty 'SW' aluminum shutters can be manual or motor operated.

Insulated Closure Panels

- Constructed with plastic frame and 3/4" polystyrene foam between outer layers of plastic double-walled sheeting.
- IC panels sized to replace the shutter during the winter months.
- Custom sizes are available.

SHIC © Copyright Munters Corporation

Shutters and Insulated Closure Panels

Custom configure your Aerotec fans with shutters and insulated closure panels. Keep your buildings draft-free with heavy duty shutters for warm weather and insulated closure panels during the cold weather. Tight-fitting shutters prevent backdrafts and air leaks, yet open easily and completely for maximum airflow when the fan is operating.



Munters Corporation, Business Area AgHort

4215 Legion Drive Mason, MI 48854-1036 USA / Phone: +1 517-676-7070 Fax: 517-676-7078
Email: aghort.info@munters.com / www.munters.us



Aluminum Shutter



with Optional
Motor Kit; SW
Series

Plastic Shutter



PS, PZ Series
(White)
PSB, PZB Series
(Black)
Available in white or
black

Insulated Closure





Panel, IC, IR

PT Shutter

Airfoil Blades

Belled- Inlet Frames



- Rugged louver and fiberglass rod design for increased durability
- Performance enhancing Belled-Inlet frame
- Solid performance over a wide range of air flow rates
- Compatible with all Aerotech brand shutter fastening systems, making it easy for retrofit installations
- Custom sizes available, minimum order quantity required

Shutters and Closure Panels are developed and produced by Munters Corporation, Mason Michigan USA



Australia Munters Pty Limited, Phone +61 2 8843 1594, **Brazil** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation Mason, Phone +1 517 676 7070, **China** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 3052 2520, **Indonesia** Munters, Phone +62 818 739 235, **Italy** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Russia** Munters AB, Phone +7 812 448 5740, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **South Africa and Sub-Sahara Countries** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spain** Munters Spain S.A., Phone +34 91 640 09 02, **Sweden** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Turkey** Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, **USA** Munters Corporation Mason, Phone +1 517 676 7070, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & Other countries** Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11.

Your closest distributor