

Product sheet
MI-T-Dark®

- High light reduction
- Low resistance to air flow
- Shipped fully assembled
- Simple installation
- Easy to clean
- Will not corrode
- Made from ultraviolet resistant PVC

MTD © Copyright Munters Corporation

MI-T-Dark®

MI-T-Dark Light Reduction at its best



High light reduction and low air flow resistance. Munters MI-T-Dark is engineered to provide the best blackout conditions in your building. Lightweight construction means low freight costs and easy one person handling. MI-T-Dark light traps slide into standard boxes and framed openings 11" deep in the air flow direction. A 3/4" flange around the perimeter will stop edge leakage. No gaskets or extra seals are required. Additional shading and/or large overhangs outside of the MI-T-Dark light traps will improve black out conditions.

MI-T-Dark light traps are manufactured in convenient, easy to handle sizes. Standard size is 11" in the air flow direction, 12 1/8" wide and up to 72" tall. The width and length may be field or factory cut to smaller sizes.

For inlets wider than 12 1/8", MI-T-Dark light traps can be installed side by side. The corrugations will nest together to form a seal between the modules. As a result, the net width is about 11 1/2" for each MI-T-Dark trap installed side by side in long sections.



Performance Curve



The gentle bends are the key to MI-T-Dark light trap performance

MI-T-Dark is developed and produced by Munters Corporation, Mason Michigan USA



Your closest distributor

Australia Munters Pty Limited, Phone +61 2 8843 1594, **Brazil** Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, **Canada** Munters Corporation Mason, Phone +1 517 676 7070, **China** Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, **Denmark** Munters A/S, Phone +45 9862 3311, **India** Munters India, Phone +91 20 3052 2520, **Indonesia** Munters, Phone +62 818 739 235, **Italy** Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, **Japan** Munters K.K., Phone +81 3 5970 0021, **Korea** Munters Korea Co. Ltd., Phone +82 2 761 8701, **Mexico** Munters Mexico, Phone +52 818 262 54 00, **Russia** Munters AB, Phone +7 812 448 5740, **Singapore** Munters Pte Ltd., Phone +65 744 6828, **South Africa and Sub-Sahara Countries** Munters (Pty) Ltd., Phone +27 11 997 2000, **Spain** Munters Spain S.A., Phone +34 91 640 09 02, **Sweden** Munters AB, Phone +46 8 626 63 00, **Thailand** Munters Co. Ltd., Phone +66 2 642 2670, **Turkey** Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, **USA** Munters Corporation Mason, Phone +1 517 676 7070, **Vietnam** Munters Vietnam, Phone +84 8 3825 6838, **Export & Other countries** Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11.