



Product sheet
CC247 Ultra Control

- Ideal for any application
- Each stage completely flexible
- Hot key operation
- Programmable Configuration Chip
- One box system
- Unmatched lightning protection
- Pre-wired Relay Panel with 20 relays expandable to 30
- Three way ON/OFF/AUTO switches on relay panel
- Current building conditions shown on screen
- Installer password can be set for protection
- Curve for Temperature and Minimum Ventilation
- Day curve for the clocks to allow for ramping programs
- 2 separate programs for Stage 1,2,3,4,5,6

CC247 Ultra © Copyright Munters Corporation

CC247 Ultra Control

The Ultra, CC24-7 series environmental controls, offering around the clock performance. The CC24-7 Series is designed with a user friendly interface, expandability and many other features which make it the ultimate building management tool. The Ultra offers a one box, easy installation and user friendly control.

The controller is compatible with a variety of accessories that will further enhance your building management. Humidity sensors, static pressure module, backup relay box, water meters, Site Watch production management software and Agri-Alert alarm system are a few of the accessories.



Munters Corporation, Business Area AgHort

4215 Legion Drive Mason, MI 48854-1036 USA / Phone: +1 517-676-7070 Fax: 517-676-7078

Email: aghort.info@munters.com / www.munters.us



Additional Control Features

- Safety features:
 - ~ High & low static pressure alarm which can operate Tunnel Curtains, Inlets and Fans
- Track History:
 - ~ Temperature Hi/Lo
 - ~ Heater Run Time
 - ~ Relative Humidity Hi/Lo
 - ~ Static Pressure Hi/Lo
 - ~ Daily Water Consumption
 - ~ Feeder Run Time with override
- Start / Stop Temperatures:
 - ~ Summer Start/Stop temperatures
 - ~ Winter Start/Stop temperatures
 - ~ Fully adjustable for each fan, cooling & heating stage
- Inlets & Tunnel Curtains:
 - ~ Static Pressure, Potentiometer or Timer for Inlets
 - ~ Potentiometer built-in
 - ~ Timer for Inlets built-in
 - ~ Pre-opening of Inlets & Tunnel Curtain
 - ~ Adjustable parameters for temperature fluctuations
- Natural Ventilation:
 - ~ Up to 2 natural outputs
 - ~ Can run 2 independent zones
- Outputs:
 - ~ 12 Stages of Fans & Cooling
 - ~ 4 Stages of Heating
 - ~ 4 Stages of Clocks
 - ~ 2 Variable Speed Outputs built-in
 - ~ 2 Outputs for 0-10 VDC
 - ~ Tunnel Curtain
 - ~ Inlet
 - ~ Alarm Contacts
- Inputs:
 - ~ 8 Temperature Sensors
 - ~ 1 Outside Temperature Sensor
 - ~ Relative Humidity
 - ~ 2 Water Meters
 - ~ Static Pressure
 - ~ Computer Compatible with Interface

Accessories

- Humidity sensors
- Static pressure module
- Backup relay box
- Water meters
- VSM-2 Variable Speed Module
- Site Watch
 - ~ Production Managemnt Software
- Agri-Alert Alarm System



Agri-Alert Alarm System has outdoor temperature compensation, maximum surge protection, ability to track alarm history and status reports on each zone.

Site Watch Production Management Software



Track enviromental conditions, water, feed, animal weights and much more in real time, 24/7.



Increase your efficiency and profitability by providing you with a complete set of conditions in real time 24/7. Works with all Munters CC247 Series controls.



Australia Munters Pty Limited, Phone +61 2 8843 1594, Brazil Munters Brasil Industria e Comercio Ltda, Phone +55 41 3317 5050, Canada Munters Corporation Mason, Phone +1 517 676 7070, China Munters Air Treatment Equipment (Beijing) Co. Ltd, Phone +86 10 80 418 000, Denmark Munters A/S, Phone +45 9862 3311, India Munters India, Phone +91 20 3052 2520, Indonesia Munters, Phone +62 818 739 235, Italy Munters Italy S.p.A., Chiusavecchia, Phone +39 0183 52 11, Japan Munters K.K., Phone +81 3 5970 0021, Korea Munters Korea Co. Ltd., Phone +82 2 761 8701, Mexico Munters Mexico, Phone +52 818 262 54 00, Russia Munters AB, Phone +7 812 448 5740, Singapore Munters Pte Ltd., Phone +65 744 6828, South Africa and Sub-Sahara Countries Munters (Pty) Ltd., Phone +27 11 997 2000, Spain Munters Spain S.A., Phone +34 91 640 09 02, Sweden Munters AB, Phone +46 8 626 63 00, Thailand Munters Co. Ltd., Phone +66 2 642 2670, Turkey Munters Form Endüstri Sistemleri A.Ş, Phone +90 262 751 3750, USA Munters Corporation Mason, Phone +1 517 676 7070, Vietnam Munters Vietnam, Phone +84 8 3825 6838, Export & Other countries Munters Italy S.p.A., Chiusavecchia Phone +39 0183 52 11.